

1st Brushless ENDO MOTOR

by Woodpecker

MotoPex

Super mini head & Slim neck

Stronger power

Precise rotation

Lower noise


Balances Weight




GUILIN WOODPECKER MEDICAL INSTRUMENT CO., LTD.

High performance brushless motor

- Adjustable reciprocating angle (10° interval; adjustment range: 20° -400°); Accurate rotating angle reduces risk of instrument fracture and enables higher preparing efficiency.



- Smooth rotation and lower noise make treatment more endurable for patients.



- Strong power, together with accurate and stable torque output, helps to realize efficient root canal preparation.



Service life of motor:
Brushless Endo Motor=Brush Endo Motor x 10


Compatible with all mainstream file systems

Speed range : 100-1800RPM
 Torque range : 0.4-5.0N.cm
 Reciprocating angle adjustment range : 20°-400°



Super Mini Contra-angle


Super mini head with a diameter of 8mm and a height of 9.7mm brings clear vision during operation.



Normal contra angle head & neck | Woodpecker contra angle Super Mini head & Slim neck

Built-in Apex locator

Integrated length determination makes endodontic treatment safer and more efficient. Realize real-time display of file location in canal. Automatically stops or reversely rotates as soon as the file reaches the apical stop, so as to prevent perforation. Auto Start and Auto Stop functions respectively enable motor to automatically start while the file gets in canal and stop when it is out.



2000mAh Lithium battery

360° rotatable contra-angle

6:1 Contra-angle

Front center-of-gravity



The choice of millions of dentists worldwide

Guilin Woodpecker Medical Instrument Co.,Ltd.
 Information Industrial Park, Guilin National High-Tech Zone, Guilin, Guangxi, 541004 P.R. China

Tel: +86-773-5873196 +86-773-20350599
 Fax: +86-773-5822450
 E-mail: woodpecker4@glwoodpecker.com
 Website: www.glwoodpecker.com

EC REP MedNet GmbH
 Borkstrasse 10-48163 Muenster-Germany