

User-friendly
Operation Interface
More Convenient For Daily Practice


Mode selection

Power varies as per different bone quality



Easy rinse

After each use, rinse the pipeline via control of foot pedal



Power / Water adjustment

Different power/water flow adjustment levels to choose from



Cutting depth switch

Surface cortical Rhino and deep cancellous Rhino



One-touch enhancement

Increase current power by 25% with one button



Surgic Smart ENT


Piezo Bone Surgery For Rhinoplasty



Guilin Woodpecker Medical Instrument Co.,Ltd.
Information Industrial Park, Guilin National High-Tech
Zone, Guilin, Guangxi, 541004 P.R. China
Sales Dept.: +86-773-5873196/2350599
After-sales Service Dept.: +86-0773-5827898
E-mail: woodpecker4@glwoodpecker.com
Website: http://www.glwoodpecker.com

EC REP MedNet EC-REP C llb GmbH
Borkstrasse 10 · 48163 Muenster · Germany

DISTRIBUTED BY:



ENH-XC-149 V1.0

INTELLIGENT AND POWERFUL

Minimally Invasive Cutting

Small wounds reduce surgical trauma, facilitating post-operative recovery

Selective cutting without damaging soft tissue

Precision















Small tip size allows precise targeting of the surgical area



PROFESSIONAL & RELIABLE


Expertly designed tips
Meet diverse usage needs

Basic Kits

- | | |
|--|---|
| 
SS1L
Left-curved tip with a longer extension, designed for oblique bone cutting in deep areas | 
SS1R
Right-curved tip with a longer extension, designed for oblique bone cutting in deep areas |
| 
SS2
For bone cutting | 
SS13
For bone cutting |
| 
SS16
For horizontal bone cutting | 
SS17
For bone trimming and osteoplasty |
| 
SS21
For bone cutting | 
SS25
For bone cutting |
| 
SS11L
Left-curved tip, used for oblique bone cutting | 
SS11R
Right-curved tip, used for oblique bone cutting |
| 
SL4
Diamond-coated head, used for fine bone trimming | 
SP7
For bone drilling |
| 
SP8
For efficient bone trimming | 
SP9
For fine bone trimming |

Smart Control System

- 1 Automatic identification of different bone quality and strength to perform power adjustment, achieving the optimal output to avoid overheating
- 2 Improved cutting efficiency, easy and effort-saving for doctors
- 3 Less noise at work



STRONG POWER

Ultra-quiet peristaltic pump

Continuous and precise flow control; direct water flow to the tip end; efficient cooling More silent and stable



New enhanced handpiece
Strong power, no handpiece overheating



Multi-function foot pedal
Control of multiple functions
One-button rinse mode



Sterilizable water pipe

External handpiece for easy disassembly and maintenance
Autoclavable

